

Manifold block VABM-B10-25E-N12-6-P3

Part number: 8026292

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	27.5 mm
Mounting position	optional
Max. number of valve positions	6
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1662 g
Type of mounting	With through-hole
Pilot air port 12	1/8 NPT
Pneumatic connection, port 1	1/2 NPT
Pneumatic connection, port 3	1/2 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy