

Common supply manifold VABM-B10-30-N34-9-P53

Part number: 8026354

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	32 mm
Mounting position	optional
Max. number of valve positions	9
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1927 g
Type of mounting	Via mounting bracket
Pneumatic connection, port 1	3/4 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy