

# Mounting NEAU-A-N8-1

Part number: 8032868

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	1
Design	For T-slot
Type of mounting	Clamped in T-slot Parallel and at right angles to the T-slot Insertable in the slot from above
Ambient temperature	-25 °C ... 85 °C
Storage temperature	-25 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material housing	Reinforced PA
Material screws	High-alloy stainless steel
Material slot nut	Nickel-plated brass