

# Mounting NEAU-A-N8-2

Part number: 8032869

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value  |
|--------------------------------|--|
| Size                           | 2  |
| Design                         | For T-slot   |
| Type of mounting               | Clamped in T-slot<br>Parallel and at right angles to T-slot<br>Insertable in the slot from above |
| Ambient temperature            | -25 °C ... 85 °C   |
| Storage temperature            | -25 °C ... 85 °C   |
| LABS (PWIS) conformity         | VDMA24364-B2-L   |
| Note on materials              | RoHS-compliant   |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress  |
| Material housing               | PA-reinforced  |
| Material screws                | High-alloy stainless steel   |
| Material slot nut              | Nickel-plated brass  |