

Sub-base VMPAL-AP-10-T1-RV

Part number: 8035231

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Construction width	10 mm
Width	10.7 mm
Length	107.3 mm
Grid dimension	10.7 mm
Pressure-zone division	Duct 1
Max. number of valve positions	1
Integrated function	Check valve
Flow direction	Non-reversible
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Suitability for vacuum	no
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 50 °C
Product weight	25 g
Pneumatic connection, port 2	For 10 mm cartridge
Pneumatic connection, port 4	For 10 mm cartridge
Note on materials	RoHS-compliant
Material sub-base	PA-reinforced