

Plastic tubing PAN-R-28X2,5-SW

Part number: 8036208

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	28 mm
Flow-relevant bending radius	350 mm
Inside diameter	23 mm
Operating pressure complete temperature range	-0.095 MPa ... 0.8 MPa
Operating pressure complete temperature range	-0.95 bar ... 8 bar
Operating pressure complete temperature range	-13.775 psi ... 116 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.4 MPa
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Temperature-dependent operating pressure	-13.775 psi ... 203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C ... 80 °C
Product weight according to length	0.207 kg/m
Pneumatic connection	For push-in connector O.D. 28 mm
Colour	Black
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A