

Cabinet through feed NEFU-D12G4-R3DW4

Part number: 8040457

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Length	40.1 mm
Conforms to standard	EN 61076-2-101 IEC 60603-7-3
Type of mounting	Screw-clamped
Electrical connection 1	Straight socket, M12x1, 4-pin, D-coded
Electrical connection 2	Angled socket, RJ45, 4-pin
Operational voltage range DC	0 V ... 30 V
Current rating at 40° C	2 A
Immunity to surge	0.8 kV
Transmission characteristics	In accordance with category 5, EN 50173, class D In accordance with category 5, ISO/IEC 11801, class D
Degree of protection	IP20 IP65 IP67
Ambient temperature	-5 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material housing	Brass, nickel-plated PA Die-cast zinc
Housing colour	Black
Material electrical contact	Brass Bronze