


# Sub-base VABS-K1-7B-12-M5-P

Part number: 8047064

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	1.2 mm
Valve size	7 mm
Fluid connection	Female thread M5
Mounting position	optional
Design	Connection direction downwards
Flow direction	Reversible
Operating medium	Liquid media Gaseous media
Note on operating and pilot medium	Observe resistance of materials that come into contact with the media
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Suitable for use with food	See supplementary material information
Media temperature	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Max. tightening torque for valve mounting	0.15 Nm
Max. tightening torque for fitting	0.6 Nm
Product weight	3.3 g
Mounting method for sub-base	With through-hole
Mounting method for valve	Via female thread
Note on materials	RoHS-compliant
Material sub-base	PEEK
Material threaded sleeve	High-alloy stainless steel