

# Check valve VABF-L1-14-H2

Part number: 8047365

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve size	14 mm
Valve function	Piloted non-return function
Operating pressure	0.05 MPa ... 0.8 MPa
Operating pressure	0.5 bar ... 8 bar
Approval	c UL us - Recognised (Oil)
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 60 °C
Product weight	1 g
Type of mounting	Grooved
Note on materials	RoHS compliant