


# Roller lever VAOM-R4-20-D1-32

Part number: 8049235

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Width	20 mm
Type of actuation	Mechanical
Mounting position	Movement plane
Design	Roller lever
Type of piloting	Direct
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Type of mounting	Screw-clamped
Note on materials	RoHS-compliant
Material mounting adaptor	Galvanised steel