

Parallel kit EAMM-U-86-S48-82AA-177

Part number: 8059021

FESTO



Data sheet

 [General operating condition](#)

| Feature | Value |
|---------------------------------------|-----------------------|
| Size | 86 |
| Mounting position | optional |
| Max. rotational speed | 5000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 175 kgmm ² |
| Frictional torque independent of load | 0.25 Nm |
| Transmittable torque | 9.5 Nm |
| Product weight | 3300 g |
| Interface code, actuator | S48 |
| Interface code, motor in | 82AA |
| Note on materials | RoHS-compliant |