


Parallel kit EAMM-U-110-S62-88A-120

Part number: 8059052

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	110
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	799 kgmm ²
Frictional torque independent of load	0.3 Nm
Transmittable torque	9.5 Nm
Product weight	5250 g
Interface code, actuator	S62
Interface code, motor in	88A
Note on materials	RoHS-compliant