


# Parallel kit EAMM-U-110-S62-88A-207

Part number: 8059058

FESTO



## Data sheet

 [General operating condition](#)

Feature	Value
Size	110
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	799 kgmm <sup>2</sup>
Frictional torque independent of load	0.3 Nm
Transmittable torque	9.5 Nm
Product weight	6900 g
Interface code, actuator	S62
Interface code, motor in	88A
Note on materials	RoHS-compliant