

Quick coupling plug NPHS-S6-M-G12F

Part number: 8059264

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	7.85 mm
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Standard nominal flow rate (standardised to DIN 1343)	1038 l/min ... 2050 l/min
Nominal flow rate standardised according to ISO 8778	1125.2 l/min ... 2222.2 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	49 g
Pneumatic connection, port 1	Female thread G1/2
Note on materials	RoHS-compliant
Information on materials	Galvanised steel