

# Fixed flow restrictor-SET VFFG-T-F6-A-V1

Part number: 8062201

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve function	Flow control function
Type of mounting	Grooved
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Ambient temperature	-5 °C ... 60 °C
Approval	c UL us - Recognised (Oil)
Size	for $\varnothing$ 5.8 mm
Nominal size	0.7 mm ... 1.8 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 40 °C
Note on materials	RoHS compliant