


# Axial kit EAMM-A-L95-120GA

Part number: 8063529

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal length	65.4 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	374 kgmm <sup>2</sup>
Transmittable torque	120 Nm
Product weight	2676 g
Interface code, actuator	L95
Interface code, motor in	120GA
Note on materials	RoHS-compliant