

# Reducing sleeve NPFC-R-G12-G18-F

Part number: 8069222

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Size of pack	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 150 °C
Product weight	43 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/8
Note on materials	RoHS-compliant