

# Operator unit CDSB-A1

Part number: 8070984

FESTO



 General operating condition

## Data sheet

Feature	Value
Max. cable length	3 m
User memory	3 GB
Display	Colour TFT
Display characteristics	Touchscreen
Display size	1.77"
Operational voltage range DC	4.5 V ... 5.5 V
Display resolution	128x160 pixels
Approval	RCM trademark
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Relative air humidity	Max. 95% at 60°C Non-condensing
Degree of protection	IP20
Ambient temperature	0 °C ... 60 °C
Product weight	36.6 g
USB interface, connection technology	USB 2.0 type B mini
Note on materials	RoHS-compliant
Material housing	PA6 reinforced
Area of application	Only with CMMT, CPX-E-CEC
Dimensions (W x L x H)	50 x 45 x 19.6 mm