


Shock absorber DYSS-2-4-Y1F

Part number: 8081767

FESTO



 General operating condition

Data sheet

Feature	Value
Size	2
Stroke	4 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Symbol	00991495
Max. impact speed	0.5 m/s
Reset time at room temperature	0.5 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 70 °C
Cushioning length	4 mm
Max. stop force	60 N
Max. tightening torque	0.5 Nm
Max. energy consumption per stroke	0.1 J
Max. energy consumption per hour	270 J
Max. residual energy	0.003 J
Reset force	0.7 N
Min. insertion force	2.5 N
Product weight	1 g
Load range	0.8 kg
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel