

Coupling EAMD-32-32-14-16X20-U

Part number: 8086051

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	14 mm
Mounting diameter 2	16 mm
Size	32
Nominal length	32 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	14.5 kgmm ²
Transmittable torque	16 Nm
Product weight	124 g
Note on materials	RoHS-compliant