

Manifold block VABS-P4-20S-G38

Part number: 8087328

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Construction width	25 mm
Mounting position	optional
Design	Connection direction at side
Max. number of valve positions	1
Operating pressure	0 bar ... 7 bar
Operating medium	Inert gas Air
Note on operating and pilot medium	Lubricated operation not possible Maximum particle size 10 µm
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C ... 80 °C
Media temperature	5 °C ... 50 °C
Ambient temperature	5 °C ... 50 °C
Product weight	97 g
Type of mounting	With through-hole
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Note on materials	RoHS-compliant
Material sub-base	Anodised wrought aluminium alloy