

Stroke reduction VAVA-F12-H-H1

Part number: 8089993

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	Opening stroke limitation
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Instructions on use	The SIL certification for the entire product is invalidated when used with angle seat valve VZXA.
Degree of protection	IP6X
Ambient temperature	-50 °C ... 100 °C
Storage temperature	-10 °C ... 60 °C
Mounting position	optional
Product weight	253 g
Note on materials	RoHS-compliant
Material seals	EPDM
Material nut	High-alloy stainless steel
Material screws	High-alloy stainless steel
Material shock absorber	High-alloy steel
Material connector	High-alloy stainless steel