

# Memory card CAMC-M-MS-G32-G2

Part number: 8094425

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-25 °C ... 85 °C
Note on materials	RoHS-compliant
Memory capacity	3.2E10 Byte
Instructions on use	The device has been developed, designed and built exclusively for industrial and commercial use. The device has not been authorised for private use.
Design	microSDHC
Design	MLC
Speed class	Class 10
Max. reading speed	70 MB/s
Max. writing speed	50 MB/s
Number of write-/erase cycles	96 TBW