

Parallel kit EAMM-U-45-V25-42AB-63

Part number: 8095562

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	45
Centre-to-centre distance	63 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	3600 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Mass moment of inertia	4.35 kgmm ²
Frictional torque independent of load	0.05 Nm
Transmittable torque	0.5 Nm
Product weight	247 g
Interface code, actuator	V25
Interface code, motor in	42AB
Note on materials	RoHS-compliant