

Parallel kit EAMM-U-65-T42-60AB-87

Part number: 8096187

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------------|------------------------|
| Size | 65 |
| Centre-to-centre distance | 87 mm |
| Mounting position | optional |
| Gear unit ratio | 1:1 |
| Max. rotational speed | 3000 rpm |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Storage temperature | -20 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Degree of protection | IP40 |
| Ambient temperature | 0 °C ... 50 °C |
| Mass moment of inertia | 41.2 kgmm ² |
| Frictional torque independent of load | 0.22 Nm |
| Transmittable torque | 3 Nm |
| Product weight | 582 g |
| Interface code, actuator | T42 |
| Interface code, motor in | 60AB |
| Note on materials | RoHS-compliant |