

Coupling EAMC-30-32-6-12

Part number: 8099435

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|------------------------|
| Mounting diameter 1 | 6 mm |
| Mounting diameter 2 | 12 mm |
| Size | 30 |
| Nominal length | 32 mm |
| Mounting position | optional |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 5.87 kgmm ² |
| Transmittable torque | 6.5 Nm |
| Product weight | 45 g |
| Note on materials | RoHS-compliant |