

Position indicator SAMH-F12-MK-A2

Part number: 8101084

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|---|
| Mounting position | optional |
| Design | 2 proximity switches with explosion protection and high level of IP protection |
| Explosion protection | Zone 2 (ATEX) Zone 22 (ATEX) |
| Instructions on use | The SIL certification for the entire product is invalidated when used with angle seat valve VZXA. |
| Note on materials | RoHS-compliant |
| Ambient temperature | -20 °C ... 60 °C |
| Storage temperature | -10 °C ... 60 °C |
| Product weight | 151 g |
| Material seals | EPDM |
| Material housing | Aluminium PA-reinforced |
| Degree of protection | IP65 IP67 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |