

# Stroke reduction VAVA-F12-H-H6

Part number: 8107369

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Design	Opening stroke limitation with cushioning
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Instructions on use	The SIL certification for the entire product is invalidated when used with angle seat valve VZXA.
Degree of protection	IP6X
Ambient temperature	-10 °C ... 80 °C
Storage temperature	-10 °C ... 60 °C
Mounting position	optional
Product weight	249 g
Note on materials	RoHS-compliant
Material seals	EPDM
Material nut	High-alloy stainless steel
Material screws	High-alloy stainless steel
Material shock absorber	High-alloy steel
Material connector	High-alloy stainless steel