

Shock absorber DYSS-G8-3-4-Y1F-G2

Part number: 8111383

FESTO



 General operating condition

Data sheet

Feature	Value
Size	3
Stroke	4 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Symbol	00991495
Max. impact speed	1 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 80 °C
Cushioning length	4 mm
Max. stop force	80 N
Max. tightening torque	1 Nm
Max. energy consumption per stroke	0.4 J
Max. energy consumption per hour	4500 J
Max. residual energy	0.004 J
Reset force	0.5 N
Min. insertion force	3.5 N
Product weight	7.8 g
Load range	1 kg
Type of mounting	Via threaded sleeve
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel
Material piston rod	High-alloy steel