

# Coupling EAMC-30-32-8-12

Part number: 8115760

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	8 mm
Mounting diameter 2	12 mm
Size	30
Nominal length	32 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	5.87 kgmm <sup>2</sup>
Transmittable torque	12.5 Nm
Product weight	48 g
Note on materials	RoHS-compliant