

Solenoid valve VSNC-F-P53U-M-G14-F19A

Part number: 8116406

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/3-way, pressurised |
| Type of actuation | Electric |
| Construction width | 32 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 950 l/min |
| pneumatic working port | NAMUR port pattern |
| Operating voltage | Via solenoid coil, must be ordered separately |
| Operating pressure | 0.3 MPa ... 0.8 MPa |
| Operating pressure | 3 bar ... 8 bar |
| Design | Piston gate valve |
| Type of reset | Mechanical spring |
| Exhaust-air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | optional |
| Conforms to standard | VDI/VDE 3845 (NAMUR) |
| Manual override | None |
| Type of piloting | Pilot actuated |
| Pilot air supply | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991083 |
| lap | Overlap |
| b value | 0.5 |
| C value | 2.1 l/sbar |
| Switching time off | 390 ms |
| Switching time on | 440 ms |
| Switching time reversal | 435 ms |
| Duty cycle | 100% |
| Characteristic coil data | See solenoid coil, to be ordered separately |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media temperature | -20 °C ... 60 °C |
| Ambient temperature | -20 °C ... 60 °C |
| Product weight | 619 g |
| Type of mounting | With through-hole |

| Feature | Value |
|------------------------------|-------------------------|
| Breather connection | Not ducted |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | NAMUR port pattern |
| Pneumatic connection, port 3 | G1/4 |
| Pneumatic connection, port 4 | NAMUR port pattern |
| Pneumatic connection, port 5 | G1/4 |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material housing | Wrought aluminium alloy |
| Material screws | Galvanised steel |