


Solenoid coil VACC-S18-35-K4-1UF-NE4ME

Part number: 8118256

FESTO



 General operating condition

Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Switching position indicator	no
Internal fuse	Fuse
Duty cycle	100%
Insulation material class	H
Characteristic coil data	24 V DC: 3.5 W 24 V AC: 50/60 Hz, power 3.5 VA
Permissible voltage fluctuations	-15%/+10%
Explosion protection certification outside the EU	EPL Db (CN) EPL Gb (CN)
Explosion protection	Zone 1 (CN) Zone 21 (CN)
Certificate issuing authority	GYJ23.1169X
Explosion ignition protection type for gas	Ex eb mb IIC T5/T6 Gb
Explosion ignition protection type for dust	Ex tb IIIC T95°C/T80°C Db
Explosion ambient temperature	T5, T95°C: -25°C ≤ Ta ≤ +60°C T6, T80°C: -25°C ≤ Ta ≤ +50°C
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP66
Product weight	580 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	RoHS-compliant