

Media separated solenoid valve VYKB-F10-M22C-16-PV-5HPA

Part number: 8122802

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Design	Rocker valve with diaphragm seal
Sealing principle	Soft
Material in contact with the medium	FPM PEEK
Valve function	2/2-way, closed, monostable
Nominal size	1.6 mm
Flow direction	Non-reversible
Type of actuation	Electric
Type of piloting	Direct
Type of reset	Mechanical spring
Manual override	None
Mounting position	optional
Type of mounting	Via through-hole for M2 screw
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connector system	Connection pattern HP
Size	10
Fluid connection	Flange
Medium	Liquid media Gaseous media
Note on the medium	Observe resistance of materials that come into contact with the media Maximum particle size 5 µm
Internal volume	35 µl
Media temperature	0 °C ... 50 °C
Media temperature for fluids	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Storage temperature	-20 °C ... 70 °C
Medium pressure	-0.075 MPa ... 0.1 MPa
Medium pressure	-0.75 bar ... 1 bar
Medium pressure	-10.875 psi ... 14.5 psi
Overload pressure	0.3 MPa
Overload pressure	3 bar
Overload pressure	43.5 psi
Operational voltage range DC	12 V
Permissible voltage fluctuations	-5% / +10%
Characteristic coil data	12 V DC: low-current phase 1 W, high-current phase 3.7 W
Duty cycle	100%

Feature	Value
Max. switching frequency	2 Hz
Switching time on	≤15 ms
Switching time off	≤15 ms
Flow rate Kv	0.034 m³/h
Symbol	00997351
Material housing	PEEK
Material membrane	FPM
Material seals	FPM
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Product weight	18 g
Degree of protection	IP40
Corrosion resistance class CRC	0 - No corrosion stress
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions