

# Retaining bracket CAFM-D4-W

Part number: 8127358

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Width	216 mm
Height	97 mm
Length	345 mm
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Ambient temperature	0 °C ... 40 °C
Product weight	749 g
Type of mounting	Threaded
Note on materials	RoHS-compliant
Material mounting bracket	Powder-coated steel