

# Angle kit EHAM-AK-L9-120-L9-120-ML

Part number: 8128208

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                      |
|--------------------------------|----------------------------|
| Size                           | 120                        |
| Mounting position              | Left                       |
| Design                         | Standard version           |
| Corrosion resistance class CRC | 0 - No corrosion stress    |
| LABS (PWIS) conformity         | VDMA24364-B2-L             |
| Ambient temperature            | -10 °C ... 80 °C           |
| Product weight                 | 5313 g                     |
| Type of mounting               | Via through-hole and screw |
| Interface code, basis          | L9-120                     |
| Interface code, setup          | L9-120                     |
| Note on materials              | RoHS-compliant             |
| Material adapter plate         | Anodised aluminium         |
| Material screws                | Nickel-plated steel        |
| Material centering elements    | High-alloy steel           |