

Angle kit EHAM-AK-L9-120-L9-90-MR

Part number: 8128214

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|----------------------------|
| Size | 120 |
| Mounting position | Right |
| Design | Standard version |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 4120 g |
| Type of mounting | Via through-hole and screw |
| Interface code, basis | L9-120 |
| Interface code, setup | L9-90 |
| Note on materials | RoHS-compliant |
| Material adapter plate | Anodised aluminium |
| Material screws | Nickel-plated steel |
| Material centering elements | High-alloy steel |