

# Shock absorber DYEF-G8-M4-Y1-F1A

Part number: 8131070

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	M4
Stroke	0.9 mm
Cushioning	Elastic cushioning rings/pads at both ends without metal fixed stop
Mounting position	optional
Position detection	Without
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Max. impact speed	0.8 m/s
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Cushioning length	0.9 mm
Max. tightening torque	0.5 Nm
Max. energy consumption per stroke	0.018 J
Product weight	5 g
Type of mounting	Via threaded sleeve
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	High-alloy steel