

Position indicator SASF-S3-B-F-A30

Part number: 8140397

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Rotation angle adjustment range	0 deg ... 180 deg
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 2
Dimensions (W x L x H)	Ø 40 x 43
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-25 °C ... 70 °C
Product weight	26 g
Type of mounting	To VDI/VDE 3845
Housing colour	Black
Note on materials	RoHS-compliant
Material spacer	PP
Material housing	PP High-alloy stainless steel
Material screws	High-alloy stainless steel