

Connection kit DADG-AK-G8-20-125

Part number: 8159796

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Size | 20 |
| Stroke | 125 mm |
| Operating pressure | 0.1 MPa ... 0.8 MPa |
| Operating pressure | 1 bar ... 8 bar |
| Operating pressure | 14.5 psi ... 116 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 3 Nm |
| Tolerance for tightening torque | ±10% |
| Max. tightening torque pneumatic connection 1 | 3 Nm |
| Product weight | 54.2 g |
| Pneumatic connection | G1/8 |
| Material adapter | Epoxy resin |
| Material seals | FPM |
| Material screws | Coated steel |