

Push-on flange DARF-Q13-25-1

Part number: 8163624

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	25
Mounting position	optional
Design	Adapter for rotary drive
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 9 according to ISO 14644-1
Ambient temperature	0 °C ... 60 °C
Max. bending moment	10 Nm
Max. axial load static	450 N
Product weight	94 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material flange	Anodised wrought aluminium alloy
Material sleeve	High-alloy stainless steel
Material screws	Coated steel