

Axial kit EAMM-A-X62-100A

Part number: 8164656

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	optional
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transmittable torque	47 Nm
Product weight	1428 g
Interface code, actuator	X62
Interface code, motor in	100A
Note on materials	RoHS-compliant