

# Coupling EAMD-56-46-22-23X27-U

Part number: 8164974

FESTO



 [General operating condition](#)

## Data sheet

| Feature                | Value                 |
|------------------------|-----------------------|
| Mounting diameter 1    | 22 mm                 |
| Mounting diameter 2    | 23 mm                 |
| Size                   | 56                    |
| Nominal length         | 46 mm                 |
| Mounting position      | optional              |
| Max. rotational speed  | 5500 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C ... 60 °C      |
| Relative air humidity  | 0 - 95%               |
| Ambient temperature    | -25 °C ... 60 °C      |
| Mass moment of inertia | 151 kgmm <sup>2</sup> |
| Transmittable torque   | 72 Nm                 |
| Product weight         | 413 g                 |
| Note on materials      | RoHS-compliant        |