

# Rod clevis CRSG-M4

Part number: 8165295

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	M4
Mounting position	optional
Based on standard	ISO 8140
Conforms to standard	DIN 71752
Threaded connection	Female thread M4
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Product weight	8 g
Material rod clevis	High-alloy steel
Note on materials	RoHS-compliant
Material bolt	High-alloy steel
Material nut	High-alloy steel
Material lock	High-alloy steel