

# Sensor mounting DASP-V4-12-A-R1

Part number: 8174844

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	12
Design	For tie rod
Mounting position	optional
For piston diameter	Ø80 Ø100 Ø125
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 120 °C
Tightening torque	0.6 Nm ... 1 Nm
Product weight	39 g
Type of mounting	Clamped
Note on materials	RoHS-compliant
Material retaining bracket	High-alloy stainless steel
Material screws	High-alloy stainless steel