

Guide unit FEN-25-50-KF

Part number: 8204034

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	25
Stroke	50 mm
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Explosion protection	The information in the certificate must be observed!
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 80 °C
Max. force F _y	520 N
Max. force F _y static	830 N
Max. force F _z	520 N
Max. force F _z static	830 N
Max. moment M _x	15 Nm
Max. torque M _x static	24 Nm
Max. moment M _y	20 Nm
Max. torque M _y static	31 Nm
Max. moment M _z	20 Nm
Max. torque M _z static	31 Nm
Displacement force	15 N
Moving mass	329 g
Product weight	873 g
Type of mounting	Via female thread
Note on materials	RoHS-compliant
Material guide component	Tempered steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Anodised wrought aluminium alloy