

Plastic-coated metal tube PM-4

Part number: 9084

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	6 mm
Flow-relevant bending radius	19 mm
Inside diameter	3.92 mm
Temperature-dependent operating pressure	-0.95 bar ... 30 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-29 °C ... 65 °C
Product weight according to length	0.024 kg/m
Colour	Black
Note on materials	RoHS-compliant
Material tubing	Wrought aluminium alloy PE