

# Rod eye SGS-M20X1,5

Part number: 9264

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	M20x1.5
Based on standard	ISO 12240-4
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	468 g
Note on materials	RoHS-compliant
Material of outer ring	Brass
Material housing	Galvanised steel
Material of inner raceway	Steel
Material nut	Galvanised steel