

Bulkhead quick connector QCK-M5-PK-3-B

Part number: 9424

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	2.4 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Bulkhead
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal torque	1.33 Nm
Tolerance for nominal tightening torque	±20%
Pneumatic connection, port 1	Female thread M5
Pneumatic connection, port 2	For tubing outside diameter of 4 mm For barbed fitting I.D. 3 mm with nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS compliant
Material nut	Galvanised steel
Material connector	Wrought aluminium alloy, anodised