

Adapter AD-1/2NPT-G1/2-I

FESTO

Part number: 9627



 [General operating condition](#)

Data sheet

| Feature | Value |
|-----------------------------------------------|--------------------------|
| Nominal size | 14.3 mm |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque pneumatic connection 1 | 28 Nm |
| Max. tightening torque pneumatic connection 2 | 40 Nm |
| Product weight | 48.48 g |
| Pneumatic connection, port 1 | Male thread 1/2 NPT |
| Pneumatic connection, port 2 | Female thread G1/2 |
| Note on materials | RoHS-compliant |
| Material seals | PVC |
| Material housing | Galvanised steel |