

# Double nipple E-G1/8-1/8NPT

Part number: 9630

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                       | Value                                    |
|---|--|
| Nominal size                                  | 5.95 mm                                  |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar                     |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7::-] |
| Note on operating and pilot medium            | Lubricated operation possible            |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                 |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L                        |
| Ambient temperature                           | -10 °C ... 60 °C                         |
| Max. tightening torque pneumatic connection 1 | 6 Nm                                     |
| Max. tightening torque pneumatic connection 2 | 7 Nm                                     |
| Nominal torque                                | 10.55 Nm                                 |
| Tolerance for nominal tightening torque       | ± 20%                                    |
| Product weight                                | 9.1 g                                    |
| Pneumatic connection, port 1                  | G1/8                                     |
| Pneumatic connection, port 2                  | 1/8 NPT                                  |
| Note on materials                             | RoHS-compliant                           |